










Top opening isothermal container for the transport of hot, chilled and frozen meals

- Maximum flexibility of use. It can carry:
 - a pan GN1/1 H 200 mm and submultiples + a eutectic plate;
 - 6 ice cream pans with capacity of 4.75 litres; 48 disposable foils 18x18 cm.
- Easy to handle, thanks to its small size and weight and the convenient carry handles.
- Capacity: 49 litres.
- It assures proper temperature retention, limiting the risk of bacterial proliferation whilst preserving food quality and organoleptic characteristics.
- The isothermal characteristics comply with current regulations (EC Reg. 852/2004 HACCP-) and with applicable technical standards (EN 12571 and Accord AFNOR AC D40-007).
- Easily stacked and transferred, thanks to the Maxidolly trolley.
- Produced with rotational moulding technology: the container and the lid have a monolithic structure (no sharp corners, junctions and welds).
- Designed to be long lasting: performance remains basically unaltered when reused.
- Fully recyclable at the end of the operating life.

MANUFACTURING MATERIALS						
Polyethylene	inner and outer walls of the container and of the lid; food contact safe	Polyurethane	insulating material between the walls of the container and of the lid free of CFC and HCFC			
Silicone rubber	gasket	Fiberglass reinforced polyamide	latches			
Stainless steel	carry handles	POM acetalic resin	handles covers			

CHARACTERISTICS It can carry pans h200 GN1/1 and submultiples. For example: 1 GN 1/1; 2 GN 1/2; It can carry: 3 GN 1/3; 1 GN1/1 + 1 eutectic4 GN 1/4; plate; 6 GN 1/6; 6 ice cream pans with capacity of 4.75 litres; 1 GN 1/2 + 48 disposable foils 18x18 2 GN 1/4; cm. 1 GN 1/3 + 4 GN 1/6; 2 GN 1/3+ 2 GN 1/6; Eutectic plates: hot (red) chilled (pink) superchilled (white) Melform closures in frozen (blue) shockproof material. extra frozen (green) to increase temperature retention performance over time (on request). Maxidolly trolley: capacity 150 Kg; 4 rubber coated, antitracking castors with PP Stainless steel carry handles core; with handle cover. castors dia: 100 mm; 2 fixed castors; 2 swivel castors. Available with chrome or stainless steel handle. Monolithic structure, no Insulated with CFC and HCFCsharp corners, junctions and welds. free polyurethane foam. USB data logger available Container guaranteed for (on request) to record use: temperature data during -30° to +100°C. transport.


TECHNICAL SPECIFICATIONS




Model	Code	Colour	External dim. (mm)	Internal dim. Ca (mm)	pacity I	Weight Kg
GN 18/18	GN180006	grey/blue melange	460x640xh380	365x545xh245	49	9.5
Hot plate GN 1/1	PEGS0003	red	530x325xh30			3
Chilled plate GN 1/1	PEGS0001	pink	530x325xh30			4
Superchilled plate GN 1/1	PEGS9001	white	530x325xh30			4
Frozen plate GN 1/1	PEGS0002	blue	530x325xh30			4
Maxidolly trolley chrome handle	MAXI0012	grey/blue melange	525x750xh965			9.4
Maxidolly trolley stainless steel handle	MAXI0011	grey/blue melange	525x750xh965			9.4
Maxidolly trolley without handle	MAXI9002	grey/blue melange	525x750xh210			7
Data logger USB	AFG007		80x33xh14			

SPARE PARTS







RRI112	RRI004	RRI019	
Locking kit (complete)	Blade only catches kit	Handle covers kit	
4 pieces per package	4 pieces per package	2 pieces per package	



Via Savigliano 34 - 12030 Monasterolo di Savigliano (CN) Tel. +39 0172812600 - Fax +39 017285991 - info@melform.com GPS: Lat 44.681363 - Long 7.624809

www.melform.com